

To: Whom may concern



Date: Feb.21,2013


Certification of Non-inclusion

Company name: OMRON SWITCH&DEVICES Corporation

Department: Quality&Environment Department

Name: Takuya Hirata

Title: General Manager

Signature: 

We hereby certify that to the best of Omron's knowledge, our products and components below (including accessories and packing materials) which we supply do not contain the chemical substances listed below at the time of shipment from the factory.

1. Chemical substances not contained:

RoHS regulated six chemical substances

- Not contained means the following substances above the maximum concentration values in homogeneous materials are not present in our products and components.

Substance	Maximum Concentration Values
Lead	0.1 wt% (1,000 ppm)
Cadmium	0.01 wt% (100 ppm)
Mercury	0.1 wt% (1,000 ppm)
Hexavalent Chromium	0.1 wt% (1,000 ppm)
Poly Brominated Biphenyls (PBB)	0.1 wt% (1,000 ppm)
Poly Brominated Diphenyl Ethers (PBDE)	0.1 wt% (1,000 ppm)

- These criteria are not applicable to the RoHS exempted items effective on the date of issue of this certificate.

2. Applicable products, components:

Category	Product Description	Category	Product Description
Dip switch	A6A Series	Dip switch	A6C Series
Dip switch	A6CN Series	Dip switch	A6CV Series
Dip switch	A6D Series	Dip switch	A6DR Series
Dip switch	A6E Series	Dip switch	A6ER Series
Dip switch	A6H Series	Dip switch	A6HF Series
Dip switch	A6HR Series	Dip switch	A6K Series
Dip switch	A6R Series	Dip switch	A6RS Series
Dip switch	A6RV Series	Dip switch	A6S Series
Dip switch	A6SN Series	Dip switch	A6SR Series
Dip switch	A6T Series	Dip switch	A6TN Series

Category	Product Description	Category	Product Description
Dip switch	A6TR Series	Rocker switch	A8A Series
Rocker switch	A8G Series	Rocker switch	A8GS Series
Rocker switch	A8L Series	Rocker switch	A8M Series
Rocker switch	A8N Series	Rocker switch	A8W Series
Push switch	A9P Series	Push switch	A9PS Series
Slide switch	A9S Series	Toggle switch	A9T Series
Toggle switch	A9TS Series	Key top	B32 Series
Tactile switch	B3AL Series	Tactile switch	B3D Series
Tactile switch	B3DA Series	Tactile switch	B3EA Series
Tactile switch	B3F Series	Tactile switch	B3FS Series
Tactile switch	B3J Series	Tactile switch	B3M Series
Tactile switch	B3S Series	Tactile switch	B3SL Series
Tactile switch	B3SN Series	Tactile switch	B3U Series
Tactile switch	B3W Series	Tactile switch	B3WN Series
Touch sensor	B6T Series	Push button switch	C2U Series
Push button switch	C4V Series	Ultra sub miniature basic switch	D2A Series
Sub miniature basic switch	D2C Series	Door interlock switch	D2D Series
Ultra sub miniature basic switch	D2F Series	Ultra sub miniature basic switch	D2FC Series
Ultra sub miniature basic switch	D2FD Series	Ultra sub miniature basic switch	D2FS Series
Sealed ultra sub miniature basic switch	D2FW Series	Sealed ultra sub miniature basic switch	D2HW Series
Sealed ultra sub miniature basic switch	D2JW Series	Ultra sub miniature basic switch	D2L Series
Low-torque basic switch	D2MC Series	Ultra sub miniature basic switch	D2MQ Series
Sub miniature basic switch	D2MS Series	Sealed sub miniature basic switch	D2MS55 Series
Miniature basic switch	D2MV Series	Sealed ultra sub miniature basic switch	D2QW Series
Reed micro switch	D2RV Series	Sub miniature basic switch	D2S Series
Sealed sub miniature basic switch	D2SW Series	Sealed sub miniature basic switch	D2SW-P Series
Door interlock switch	D2T Series	Sealed miniature basic switch	D2VW Series
Connector termination switch	D2X Series	Ultra sub miniature basic switch	D3C Series
Door switch	D3D Series	Door switch	D3DC Series
Connector termination switch	D3K Series	Sub miniature basic switch	D3M Series

Category	Product Description	Category	Product Description
Sub miniature basic switch	D3MH Series	Sub miniature basic switch	D3R Series
Surface mount detection switch	D3SH Series	Surface mount detection switch	D3SJ Series
Surface mount detection switch	D3SK Series	Miniature basic switch	D3V Series
Incline sensor	D6B Series	Micro displacement sensor	D6E Series
MMS flow sensor	D6F Series	MMS thermal sensor	D6T Series
Quake sensor	D7E Series	Quake sensor	D7H Series
Switch unit	D9R Series	Pressure display	E80 Series
Pressure display	E8Y Series	Ultra sub miniature basic switch	J Series
Miniature basic switch	K Series	Miniature basic switch	L Series
Quake sensor	D7G-F Series	Thermal sensor	2SMT Series
Sub miniature basic switch	S Series	Sub miniature basic switch	SS Series
Sub miniature basic switch	SSG Series	Sub miniature basic switch	SSP Series
Sub miniature basic switch	SS-P Series	Miniature basic switch	V series
Miniature basic switch	VX series		

Note) This certificate is in conformity with the applicable requirements of 6 substances restrictions in EU Directive 2011 /65 /EU (RoHS recast).